

Product data sheet

Characteristics

AR3150HACS

APC NetShelter SX, Server Rack Enclosure,
42U, without Rear Doors, Black, 1991H x
750W x 1070D mm



Overview

Lead time Usually in Stock

Main

Number of rack unit	42U
Provided equipment	Casters Doors Ground studs Installation guide Leveling feet Mounting Hardware Roof Side Panels

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	29.53 in (75 cm)
Depth	42.13 in (107 cm)
Net Weight	313.65 lb(US) (142.27 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 14 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

GTIN	731304241560
Package weight(Lbs)	340.72 lb(US) (154.55 kg)

Packing Units

Package 1 Height	87.24 in (221.6 cm)
Package 1 width	35.24 in (89.5 cm)
Package 1 Length	47.99 in (121.9 cm)
Number of Units in Package 3	1

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------