

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Bezel material	Black plastic
Device short name	SK
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Mounting diameter	1.18 in (30 mm)

Complementary

Line Rated Current	3 A
Cap/operator or lens colour	Black
Contact operation	Power reed
Contacts type and composition	1 NO
Control type	Push-button
Electrical connection	Screw clamp terminal
Mounting support	Panel
Operator position information	2 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Permissible voltage	<= 240 V AC <= 115 V DC
Shape	Round head
Type of operator	Maintained
Utilisation category	AC-15 DC-13

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901716235
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20000000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------