



### Main

|                           |                  |
|---------------------------|------------------|
| Range of product          | Harmony 9001KS   |
| Product or component type | Selector switch  |
| Device short name         | 9001KS           |
| Type of operator          | maintained       |
| Operator profile          | Black key switch |

### Complementary

|                               |                        |
|-------------------------------|------------------------|
| Bezel material                | Chromium plated metal  |
| Mounting diameter             | 1.18 in (30 mm)        |
| Net weight                    | 0.54 lb(US) (0.245 kg) |
| Shape of signaling unit head  | Round                  |
| Operator position information | 2 positions            |
| Key number                    | E16                    |
| Key withdrawal position       | Right                  |
| Contacts type and composition | Without contact block  |
| Mechanical durability         | 500000 cycles          |
| Device presentation           | Basic element          |

### Environment

|                                       |                                                                                                                |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TC                                                                                                             |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                     |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                                                                     |
| Overvoltage category                  | Class II IEC 61140                                                                                             |
| IP degree of protection               | IP66 IEC 60529                                                                                                 |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 6                                |
| Standards                             | EN/IEC 60947-1<br>UL 508<br>JIS C 852<br>JIS C 4520<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>CSA C22.2 No 14 |
| Product certifications                | UL 508<br>NEMA                                                                                                 |
| Vibration resistance                  | 7 gn 2...500 Hz)IEC 60068-2-6                                                                                  |
| Shock resistance                      | 50 gn IEC 60068-2-27                                                                                           |

## Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                           |
| GTIN                  | 00785901705055                |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.5 lb(US) (0.23 kg)          |
| Returnability         | No                            |
| Country of origin     | MX                            |

## Packing Units

|                  |                      |
|------------------|----------------------|
| Package 1 Height | 5.08 in (12.903 cm)  |
| Package 1 width  | 2.00 in (5.080 cm)   |
| Package 1 Length | 12.90 in (32.774 cm) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                      |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                         |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                                                                                                 |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                          |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                                                                                           |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|