



Overview

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	3 phase
Provided Equipment	Installation guide

Physical

Height	9.02 in (22.9 cm)
Width	17.99 in (45.7 cm)
Depth	27.99 in (71.1 cm)
Net Weight	52.01 lb(US) (23.59 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz
Number of input connectors	1 Hard Wire 5-wire (3PH + N + G)
Acceptable Input Voltage	200...240 V
Max line current	200 A
Load Capacity	72000 VA

Output

Maximum Total Current Draw per Phase	200 A
--------------------------------------	-------

Conformance

Product Certifications	UL Listed
------------------------	-----------

Ordering and shipping details

GTIN	731304264521
Package weight(Lbs)	74.96 lb(US) (34 kg)

Packing Units

Package 1 Height	15.98 in (40.6 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	35.00 in (88.9 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------