



Overview

Lead time	Usually Ships within 6 Weeks
-----------	------------------------------

Main

Main Input Voltage	3 phase 3 phase
Battery Type	VRLA
Provided Equipment	User Manual

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	11.81 in (30 cm)
Depth	42.13 in (107 cm)
Net Weight	327.70 lb(US) (148.64 kg)
Mounting Mode	Not rack-mountable
USB compatible	No

Conformance

Product Certifications	CUL Listed CE UL Listed VDE
------------------------	--------------------------------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0

Ordering and shipping details

GTIN	731304253570
Package weight(Lbs)	411.87 lb(US) (186.82 kg)

Packing Units

Package 1 Height	84.65 in (215 cm)
Package 1 width	29.33 in (74.5 cm)
Package 1 Length	47.64 in (121 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---