



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Provided Equipment	Installation guide
--------------------	--------------------

Physical

Height	0.98 in (2.5 cm)
Width	144.09 in (366 cm)
Depth	0.98 in (2.5 cm)
Net Weight	7.28 lb(US) (3.3 kg)
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	-35...165 °F (-37...74 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...3000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	9.04 lb(US) (4.1 kg)
---------------------	----------------------

Packing Units

Package 1 Height	6.89 in (17.5 cm)
Package 1 width	14.57 in (37 cm)
Package 1 Length	11.81 in (30 cm)

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------