

Pre assembled USB programmable tower lights, Harmony XVGU, multi color, 60mm, steady flashing LED, buzzer

XVGU3SHAV

Product availability: Stock - Normally stocked in distribution facility

Main

•••••		
Range of Product	Harmony XVGU	
Product or Component Type	USB configurable monolithic tower light	
Beacon or indicator bank unit type	3 illuminated units	
Sound signalling	Buzzer	
Mounting diameter	2.4 in (60 mm)	
Component name	XVGU	
Light source	LED steady or flashing multi-colour	
Indicator bank base type	Base with integrated buzzer	
Noise level	85 dB 2 tone buzzer)1 m	

Complementary

Material	PC: globe	
Device mounting	Tube mounting with fixing plate	
Light block color	Clear/clear	
[Us] rated supply voltage	5 V DC	
Connector Type	USB type A female	
Current Consumption	400 mA	
Sound frequency	3800 Hz 2700 Hz	
Power Consumption in W	2 W	
Flashing frequency	2 Hz flashing LED unit 1 Hz flashing LED unit	
Product compatibility	Vijeo Designer 4.6 indoor use only HMIGTO XBTGT XBTGK XBTGC1. XBTGC2. XBTGH	
Net Weight	0.7 lb(US) (0.3 kg)	

Environment

Standards	IEC 61000-6-2
	IEC 61000-6-4

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	GOST
	CE
	UL 508
	cUL
	RCM
Ambient Air Temperature for Storage	-31158 °F (-3570 °C)
Ambient Air Temperature for Operation	32131 °F (055 °C)
Electrical shock protection class	Class I
IP Degree of Protection	IP54

Ordering and shipping details

Category	US100XV22618	
Discount Schedule	00XV	
GTIN	3606480530937	
Returnability	Yes	
Country of origin	ID	

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.23 in (8.200 cm)
Package 1 Width	5.12 in (13.000 cm)
Package 1 Length	16.34 in (41.500 cm)
Package weight(Lbs)	17.143 oz (486.000 g)
Unit Type of Package 2	S06
Number of Units in Package 2	30
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	58.026 lb(US) (26.320 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	21
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	6797f094-b2bf-48a4-981a-58794615fad0
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

XVGU3SHAV

Dimensions Drawings


Dimensions

Tube Mounting with Fixing Plate




Mounting and Clearance

Mounting on Horizontal Support for Tube Mounting with Fixing Plate



(1) Cable outlet

Mounting Orientation




Choose a flat surface with enough strength and with little vibration for installation. Mount this product according to the figure to maintain IP characteristics.

- (1) OK
- (2) NO

Technical Illustration

Dimensions



XVGU3SHAV

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Easy Harmony XVG

