

Socket-outlet, X Series, 15A, decorator, GFCI, tamper resistant, weatherproof, residential, white, matte finish

SQR51103WH

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Square D X Series	
Product or Component Type	Socket-outlet Socket-outlet	
Aesthetic name	X Series	
Device Application	Power supply	
Device presentation	Mechanism with fixing frame	
Body type	Decorator	
Socket number	2	
Outlet poles configuration	2P + E	
Outlet standard	NEMA	
Socket additional information	Tamper resistant	

Complementary

Device mounting	Flush	
Mounting Mode	By screws	
[le] rated operational current AC	15 A	
[Ue] rated operational voltage	125 V	
Network type	AC	
Network Frequency	60 Hz	
Number of gangs	1 gang	
Number of modules	1	
Color	White	
Surface Finish	Matte	
Material	Plastic: strap Metal: fixing frame	
Connections - terminals	Phase and neutral 4 screw terminal copper Earth 1 screw terminal copper	
Earth circuit	Self earthing	
Protection Type	GFCI	
Width	1.7 in (42 mm)	
Height	4.06 in (103 mm)	
Depth	1.6 in (41 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Quantity per Set 1 piece

Environment

Environmental characteristic	Weatherproof
Product Certifications	cULus
Standards	UL 498 UL 943
	ICES-003

Ordering and shipping details

_		
Category	US10DE909932	
Discount Schedule	0DE9	
GTIN	00785901544692	
Returnability	Yes	
Country of origin	CN	

Packing Units

Unit Type of Package 1	PCE	
Nbr. of units in pkg.	1	
Package 1 Height	4.33 in (11.0 cm)	
Package 1 Width	1.77 in (4.5 cm)	
Package 1 Length	1.97 in (5.0 cm)	
Package weight(Lbs)	4.8 oz (136.0 g)	
Unit Type of Package 2	BB1	
Number of Units in Package 2	10	
Package 2 Height	4.72 in (12.0 cm)	
Package 2 Width	4.13 in (10.5 cm)	
Package 2 Length	9.25 in (23.5 cm)	
Package 2 Weight	3.228 lb(US) (1.464 kg)	
Unit Type of Package 3	PAL	
Number of Units in Package 3	2520	
Package 3 Height	47.24 in (120.0 cm)	
Package 3 Width	39.37 in (100.0 cm)	
Package 3 Length	47.24 in (120.0 cm)	
Package 3 Weight	1003.72 lb(US) (455.28 kg)	

Contractual warranty

Warranty 2 years



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

Technical Illustration

Wiring diagram




Image of product / Alternate images

Alternative













