



### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Cable length	6.56 ft (2.00 m)
Number of cables	1
Product Compatibility	UPS

### Physical

Color	Black
Net Weight	1.01 lb(US) (0.46 kg)
Mounting Location	Front
Mounting Mode	Not rack-mountable
Connector B	SUB-D 9 male Smart Signaling
Connector A	SUB-D 9 female Smart Signaling

### Output

Number of port	1
----------------	---

### Environmental

Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)

### Ordering and shipping details

GTIN	731304316350
Package weight(Lbs)	1.01 lb(US) (0.46 kg)

### Packing Units

Package 1 Height	9.02 in (22.9 cm)
Package 1 width	4.02 in (10.2 cm)
Package 1 Length	2.01 in (5.1 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------