



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Plug standard	IEC 60320 C20
Number of rack unit	1U
Provided Equipment	Mounting Hardware Rack Mounting brackets Serial configuration cable

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.01 in (43.2 cm)
Depth	9.29 in (23.6 cm)
Net Weight	8.25 lb(US) (3.74 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Max line current	20 A
Input current limits	20 A
Load Capacity	3300 VA

Output

Maximum Total Current Draw per Phase	20 A
Number of power socket outlets	8 IEC 60320 C13 1 IEC 60320 C19
Protection Type	Without circuit breaker

Conformance

Product Certifications	CUL Listed CE UL Listed
Standards	EN 55022 Class A FCC Part 15 class A

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)




Ordering and shipping details

GTIN	731304333487
Package weight(Lbs)	12.15 lb(US) (5.51 kg)

Packing Units

Package 1 Height	4.49 in (11.4 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	14.02 in (35.6 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------