



Overview

Presentation	1U rack-mountable keyboard, mouse, and LCD console with US English keyboard layout.
Lead time	Usually in Stock

Main

Main Input Voltage	100 V 240 V
Number of rack unit	1U
Provided equipment	C13-C14 power cord Documentation CD Firmware upgrade cable Installation guide NEMA 5-15 power cord PS2 KVM cable Single user rack mount kit USB cable USB KVM cable

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	18.98 in (48.2 cm)
Depth	24.17 in (61.4 cm)
Net Weight	35.05 lb(US) (15.9 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted
Maximum Mounting Depth	41.33 in (104.98 cm)
Minimum Mounting Depth	26.77 in (68 cm)

Input

Input Frequency	50/60 Hz
-----------------	----------

Conformance

Product Certifications	C-tick CE Industry Canada KCC NOM UL Listed VDE TAA compliance
Standards	EN 55022 Class A EN 55024 EN 60950 FCC Part 15 class A IEC 60950

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
---------------------------------------	-------------------------

Supported Hardware

Display colour	16 colours
Display size	17 inch
Trackball Type	PS/2 Touchpad USB mouse
Display Type	LCD display
LCD Power Consumption	19 W
Pixel size	0.26

Ordering and shipping details

GTIN	731304283232
Package weight(Lbs)	42.90 lb(US) (19.46 kg)

Packing Units

Package 1 Height	5.98 in (15.2 cm)
Package 1 width	26.50 in (67.3 cm)
Package 1 Length	32.52 in (82.6 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------