

APDU9941

APC Rack PDU, 9000 switched, 0U, 30A, 200V and 208V, 21 C13 and C15, 3 C19 and C21 sockets



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V 200 V
PDU Type	Switched
Main Output Voltage	200 V 208 V
Input Connection Type	NEMA L6-30P
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Communication Port Protocol	SNMP Redfish
Provided Equipment	Installation guide Rack Mounting brackets Safety guide

Physical

Color	Black
Height	72.01 in (182.9 cm)
Width	2.17 in (5.5 cm)
Depth	1.81 in (4.6 cm)
Net Weight	18.74 lb(US) (8.5 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No
Mounting position	Vertical

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Input

Line Rated Current	24 A
Max line current	30 A
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	21C13/C15 3C19/C21
--------------------------------	-----------------------

Conformance

Product Certifications	CUL Listed FCC part 15 class A PSE
Standards	ICES-003

Environmental

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Batteries & Runtime

Communication Network Type	10/100/1000BASE-T
----------------------------	-------------------

Ordering and shipping details

GTIN	731304356264
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	80.31 in (204 cm)
Package 1 Width	4.88 in (12.4 cm)
Package 1 Length	6.50 in (16.5 cm)
Package 1 Weight	22.05 lb(US) (10 kg)

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------