



Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------



Main

Kw Rating	1920 W
Rated power in VA	1920 VA
Nb of power socket outlets	6 NEMA 5-15R 2 NEMA 5-20R
Output voltage	120 V
Nominal Input Voltage	120 V
Plug standard	NEMA 5-20P
Cable length	8 ft (2.44 m)
Number of cables	1

General

Number of power module filled slots	0
Number of power module free slots	0
Number of tare power	63 W
Redundant	No
Provided equipment	CD with software Documentation CD Rack Mounting brackets Smart UPS signalling RS-232 cable USB cable

Physical

Mounting Mode	Rack-mounted with kit
Mounting position	Horizontal
Mounting preference	Lower
Depth	26.89 in (68.3 cm)
Height	3.39 in (8.6 cm)
Product Weight	93.28 lb(US) (42.31 kg)
Width	18.90 in (48 cm)
Two post mountable	0
USB compatible	Yes
Color	Black

Input

Efficiency at full load	75...154 V adjustable 82...143 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	2200 VA
Max Configurable Power (Watts)	1980 W
Transfer Time	4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CSA
Equipment protection policy	Lifetime : \$150000
Standards	FCC Part 15 class A UL 1778

Environmental

Acoustic level	55 dBA
Heat dissipation	215 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Type	Lead-Acid battery
Extendable Run Time	0
Liquid Electrolyte Value	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Battery power in VAh	494 VAh runtime
Battery Charge Power (Watts)	164 W rated

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	0
Pre-Installed SmartSlot® Cards	Network management card

Surge Protection and Filtering

Surge energy rating	530 J
---------------------	-------

Ordering and shipping details

GTIN	00731304293330
Package weight(Lbs)	109.64 lb(US) (49.73 kg)

Packing Units

Package 1 Height	10.00 in (25.4 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	38.58 in (98 cm)
Number of Units in Package 3	8

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---