

SRT10KRMTF

APC Smart-UPS SRT Step-Down Transformer,
10kVA, rackmount, 4U, 2x NEMA L5-20R & 2x
NEMA L14-30R outlets



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V
Main Output Voltage	120 V 208 V 240 V
Output connector type	Hard Wire 3-wire (2PH + G) 2 Hard Wire 4-wire (2PH+N+G) 1
Provided Equipment	Mounting Hardware Rack Mounting brackets Safety guide User Manual Warranty card

Physical

Color	Black
Height	6.85 in (17.4 cm)
Width	17.01 in (43.2 cm)
Depth	29.49 in (74.9 cm)
Net Weight	220.00 lb(US) (99.79 kg)
Mounting preference	Lower
Mounting Mode	Rack-mounted
Mounting position	Horizontal

Input

Acceptable Input Voltage	200...240 V
Max line current	60 A
Input current limits	60 A
Load Capacity	10000 VA
Input Frequency	45...65 Hz
Number of input connectors	1 Hard Wire 3-wire (2PH + G)

Output

Maximum Total Current Draw per Phase	60 A
Number of power socket outlets	4
Number of power socket outlets	2 NEMA L5-20R 2 NEMA L14-30R

Conformance

Product Certifications	CE CSA UL Listed
------------------------	------------------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)


Ordering and shipping details

GTIN	731304318859
Package weight(Lbs)	275.00 lb(US) (124.74 kg)

Packing Units

Package 1 Height	15.98 in (40.6 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	39.37 in (100 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------