

# PanelSeT CRN plain door w/o mount.plate. H250xW300xD150 IP66 IK10 RAL7035..

NSYCRN23150

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range	PanelSeT	
Product name	PanelSeT CRN	
Application	Multi-purpose	
Category	Compact enclosure	
Enclosure nominal height	7.9 in (200 mm)	
Enclosure nominal width	11.8 in (300 mm)	
Enclosure nominal depth	5.9 in (150 mm)	
Installation accessory type	Wall-mounting	
Device composition	1 body 1 door 1 lock 2 cable gland plate top and bottom	
Door type	Solid	
Mounting plate description	Without mounting plate	

## Complementary

body type	Sides made from a single folded section  Back welded with double profile forming a protected sealed area	
Number of doors	Front face 1	
Door opening side	Reversible 120 °)	
Lock type	3 mm double-bar lock	
Type of gland plate	Standard	
Accessibility for operation	Front	
Removable parts	Door by hinges Cable gland plate by screws	
Material	Body steel	
Surface finish	epoxy-polyester powder	
color	Gray RAL 7035)	
Standards	IEC 62208 UL CUL	
Product Certifications	UL cUL DNV-GL	
Product Weight	7.249 lb(US) (3.288 kg)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environment**

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
GTIN	3606480212642
Returnability	No
Country of origin	ES

## **Packing Units**

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	6.69 in (17.000 cm)
Package 1 Width	8.27 in (21.000 cm)
Package 1 Length	11.81 in (30.000 cm)
Package weight(Lbs)	7.249 lb(US) (3.288 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	50
Package 2 Height	22.05 in (56.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	401.242 lb(US) (182.000 kg)

## **Contractual warranty**

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	31
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Offer Marketing Illustration

#### **Product benefits / Features**

