

Complete control station, Harmony XALD, dark grey, pushbuttons, 22mm, 2NO +1NC, marked

XALD351H29H7

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XALD	
Product or Component Type	Complete control station	
Device short name	XALD	
Product destination	For XB5 Ø 22 mm control and signalling units	
Control station application	Three functions	
Colour of base of enclosure	Light grey RAL 7035)	
Colour of cover	Dark grey RAL 7016)	
Material	Polycarbonate	

Complementary

Cable entry	2 knock-outs for cable entry 0.6 in (14 mm) 2 knock-outs for Pg 13 cable gland and ISO M20 0.5 in (12 mm)	
Resistance to high pressure washer	1015.3 psi (7000000 Pa) 131 °F (55 °C) 0.1 m	
Mechanical durability	10000000 cycles	
Connections - terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end IEC 60947-1 Screw clamp terminals, >= 1 x 0.22 mm² without cable end IEC 60947-1	
Tightening torque	7.0810.6 lbf.in (0.81.2 N.m) IEC 60947-1	
Shape of screw head	Cross Philips no 1 Cross pozidriv No 1 Slotted flat Ø 4 mm Slotted flat Ø 5.5 mm	
Contacts material	Silver alloy (Ag/Ni)	
Short-circuit protection	10 A cartridge fuse gG IEC 60947-5-1	
[Ith] conventional free air thermal current	al 10 A IEC 60947-5-1	
[Ui] rated insulation voltage	600 V 3)IEC 60947-1	
[Uimp] rated impulse withstand voltage	6 kV IEC 60947-1	
[le] rated operational current 6 A 120 V, AC-15, A600 IEC 60947-5-1 3 A 240 V, AC-15, A600 IEC 60947-5-1 1.2 A 600 V, AC-15, A600 IEC 60947-5-1 0.55 A 125 V, DC-13, Q600 IEC 60947-5-1 0.27 A 250 V, DC-13, Q600 IEC 60947-5-1 0.1 A 600 V, DC-13, Q600 IEC 60947-5-1		
Electrical durability	1000000 cycles, AC-15, 2 A 230 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 3 A 120 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 4 A 24 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.2 A 110 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.5 A 24 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Electrical reliability	Λ < 10exp(-6) 5 V 1 mA IEC 60947-5-4	
	Λ < 10exp(-8) 17 V 5 mA IEC 60947-5-4	

Environment

Protective treatment	тн	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Ambient air temperature for operation	-40158 °F (-4070 °C)	
Electrical shock protection class	Class II conforming to IEC 60536	
IP degree of protection	IP66 IEC 60529 IP69 IP69K IP67	
NEMA degree of protection	NEMA 13 NEMA 4X	
IK degree of protection	IK03 conforming to IEC 62262	
Standards	IEC 60947-5-4 IEC 60947-1 CSA C22.2 No 14 IEC 60947-5-1 UL 508 IEC 60947-5-5	
Product Certifications	CSA UL Listed	
Vibration resistance	5 gn (f= 12500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27	

Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
GTIN	3606480502712
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.80 in (7.112 cm)
Package 1 Width	3.90 in (9.906 cm)
Package 1 Length	5.60 in (14.224 cm)
Package weight(Lbs)	10.400 oz (294.835 g)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	2	

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture		
Take-back	No	

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony XALD



Image of product / Alternate images

Alternative











