

Product data sheet

Specifications



remote terminal, Altistart 22, for soft starter for asynchronous motor, IP54

VW3G22101

Main

Range of product	Altistart 22
Accessory / separate part designation	Remote terminal
IP degree of protection	IP54
Accessory / separate part type	Remote terminal
Accessory / separate part category	Control accessories
Product compatibility	ATS22
Accessory / separate part destination	Soft starter for asynchronous motor
Accessory dimension	50 x 15 x 70 mm

Complementary

Product weight	0.25 kg
----------------	---------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	6.5 cm
Package 1 Length	8.6 cm
Package 1 Weight	66.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	90
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.795 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	7161d12e-f65a-43f1-970c-ddc6260d9e62
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No