

Wall mounted steel enclosure, PanelSeT S3DC, plain door, without plain chasis, 800x600x300mm, IP66, IK10

NSYS3DC8630

Main

Range	PanelSeT	
Product name	PanelSeT S3DC	
Application	Multi-purpose	
Category	Compact enclosure	
Enclosure nominal height	800 mm	
Enclosure nominal width	600 mm	
Enclosure nominal depth	300 mm	
Door type	Plain	
Mounting plate description	Without mounting plate	
Type of gland plate	Without gland plate	
Installation accessory type	Wall-mounting	
Device composition	1 body 1 door 1 lock	

Complementary

body type	Single piece body Gutter-shaped front profile double sheet thickness	
Number of doors	Front face: 1 door(s)	
Door opening side	Reversible (120 °)	
Lock type	3 points lock, screw driver insert	
Accessibility for operation	Front	
Removable parts	Door by hinges	
Material	Steel	
Surface finish	Epoxy-polyester powder	
Colour	Grey (RAL 7035)	
Standards	IEC 62208 UL CUL	
Product certifications	UL	
Product weight	23.4 kg	

Environment

NEMA degree of protection NEMA 4X/13

IK degree of protection	IK10 conforming to IEC 62262	
IP degree of protection	IP66 conforming to IFC 60529	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	36.000 cm
Package 1 Width	62.000 cm
Package 1 Length	90.000 cm
Package 1 Weight	23.400 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	9
Package 2 Height	200.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	221.000 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Total lifecycle Carbon footprint	220
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No