# Acti9 - comb busbar - 1L - 18 mm pitch - 24 modules - 100A



A9XPH124

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range	Acti9	
Product or Component Type	Comb busbar	
Mounting Mode	Horizontal	
Accessory / separate part category	Connection accessory	
Lines description	1L	
Length in 18 mm modules	24	
Standards	EN/IEC 61439-1	

## Complementary

Number of ways	24 ways 1 L	
Distribution type	L	
Poles configuration for 1 way	1 x 1P	
Connection pitch	0.7 in (18 mm)	
Connector type	tooth	
Distance between way	0.7 in (18 mm)	
Marking	L	
Insulation	Insulated	
Device presentation	Cuttable	
[le] rated operational current	100 A 104 °F (40 °C)	
[Ue] rated operational voltage	415 V AC	
[Ui] rated insulation voltage	500 V AC IEC 61439-2	
Mounting location	Top or bottom tunnel type terminals Top or bottom double terminal	
9 mm pitches	48	
Width	16.9 in (430 mm)	
color	White RAL 9003)	
Range compatibility	Acti9 Acti9 iC60 Acti9 Acti9 iK60 Acti9 Acti9 iID Acti9 Acti9 iID K Acti9 Acti9 iSW Acti9 Acti9 iSW-NA	

## **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Multi9 Multi9 C60

Fire resistance	1760 °F (960 °C) 30 s ) IEC 60695-2-1	
Pollution degree	3 IEC 60947-7-1	
IP degree of protection	IP20 with end-pieces and tooth covers	

# Ordering and shipping details

Category	US10DE201078
Discount Schedule	0DE2
GTIN	3606480485015
Returnability	No
Country of origin	DE

## **Packing Units**

Unit Type of Package 1	PCE	
Nbr. of units in pkg.	1	
Package 1 Height	0.20 in (0.500 cm)	
Package 1 Width	1.18 in (3.000 cm)	
Package 1 Length	16.81 in (42.700 cm)	
Package weight(Lbs)	3.563 oz (101.000 g)	
Unit Type of Package 2	BB1	
Number of Units in Package 2	10	
Package 2 Height	2.36 in (6.000 cm)	
Package 2 Width	3.43 in (8.700 cm)	
Package 2 Length	18.39 in (46.700 cm)	
Package 2 Weight	2.471 lb(US) (1.121 kg)	
Unit Type of Package 3	S04	
Number of Units in Package 3	100	
Package 3 Height	11.81 in (30.000 cm)	
Package 3 Width	15.75 in (40.000 cm)	
Package 3 Length	23.62 in (60.000 cm)	
Package 3 Weight	26.004 lb(US) (11.795 kg)	

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	2
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

<b>⊗</b> Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
SCIP Number	41a8b1b0-6424-4682-ac9c-98796ac87431
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.