

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Harmony 9001K
Product or component type	Illuminated push-button
Device short name	K
Type of operator	Spring return
Operator profile	White flush
Operator additional information	Extended metallic guard

Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 in (30 mm)
Light source	Incandescent
Bulb base	BA 9s
Light block supply	Via integral transformer
[Us] rated supply voltage	220...240 V AC
Contacts type and composition	1 NO
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A (AC-15) 10 A (DC-13)
Contact operation	Standard
Device presentation	Complete product

Environment

Product certifications	CE CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR NEMA
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901287407
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------