



Main

Range of product	Multi 9
Product or component type	OC contact
Device short name	OF
Signal contacts composition	1 C/O
Line Rated Current	3 A 380...415 V AC - 50/60 Hz 6 A 220...240 V AC - 50/60 Hz 1 A 130 V DC 1.5 A 60 V DC 2 A 48 V DC 6 A 24 V DC
9 mm pitches	1

Complementary

Range compatibility	Multi 9 C60 Multi 9 C60H-DC Multi 9 C60CTRL Acti 9 DPN Vigi Acti 9 RCCB-ID Acti 9 iSW-NA
Mounting mode	Fixed
Mounting support	DIN rail
Height	3.31 in (84 mm)
Width	0.35 in (9 mm)
Depth	2.87 in (73 mm)
Connections - terminals	Clamp terminal2 0.00 in ² (1.5 mm ²) - flexible Clamp terminal2 0.00 in ² (1.5 mm ²) - rigid Clamp terminal1 0.00...0.00 in ² (0.5...2.5 mm ²) - flexible Clamp terminal1 0.00...0.00 in ² (0.5...2.5 mm ²) - rigid
Wire stripping length	0.35 in (9 mm)
Tightening torque	8.85 lbf.in (1 N.m)

Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASTA KEMA ASEFA LCIE
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 EN/IEC 60947-5-1
Relative humidity	95 % 131 °F (55 °C)
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	01078 - DE2 MISC
Discount Schedule	DE2
GTIN	00785901763338
Nbr. of units in pkg.	1
Package weight(Lbs)	0.08 lb(US) (0.04 kg)
Returnability	No
Country of origin	BE

Packing Units

Package 1 Height	0.080 dm
Package 1 width	0.018 dm
Package 1 Length	0.090 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------