



Timing Relay, Type JCK, plug In, on delay, adjustable time, 0.3 to 30 seconds, 10A, 240 VAC, 120 VAC/ 110 VDC

9050JCK12V20

Product availability: Stock - Normally stocked in distribution facility

#### Main

product range	9050JCK	
product type	Timer	
timing mode	On-delay	
timing range	0.330 s	
supply voltage	120 V AC 110 V DC	

# **Complementary**

power consumption	2 VA
current rating	10 A
switch function	DPDT
contact composition	2 NO + 2 NC
contact material	Silver nickel
maximum switching voltage	240 V AC
mounting type	Socket
number of pins	8
shape of pins	Tubular
for use with	8501NR51 8501NR52

## **Environment**

certifications	UL Recognized UL Listed CE
ambient temperature range - operational	-2866 °C (-18150 °F)
Height	2.4 in (61 mm)
Width	1.7 in (43 mm)
Depth	4.09 in (104 mm)

# Ordering and shipping details

Category	US10CP221651
Discount Schedule	0CP2
GTIN	785901032557

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes	
Country of origin	IIS	

# **Packing Units**

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	4.40 in (11.176 cm)
Package 1 Length	2.00 in (5.08 cm)
Package weight(Lbs)	4.32 oz (122.47 g)

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	50	

#### **Use Better**


Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture		
Take-back	No	

**Technical Illustration** 


#### **Dimensions**



All dimensions are approximate. Also see technical documentation.

### **Technical Illustration**

## Wiring diagram



JCK11 - JCK19

JCK31 - JCK39

JCK51 - JCK59

JCK60

Image of product / Alternate images

#### **Alternative**







