

Die cast empty control station, Harmony XAP, XB2 SL, zinc alloy, grey, 1 cut out, 22mm, 80x80x51.5mm

XAPG19201

Product availability: Stock - Normally stocked in distribution facility

### Main

Range of Product	Harmony XAP	
Product or Component Type	Die-cast empty control station	
Device short name	XAPG	
Product destination	For Ø 22 mm control and signalling units	
Number of cut-out	1 cut-out	
Colour of base of enclosure	Grey RAL 7032)	
Colour of cover	Grey RAL 7032)	
Control station type	Metal	
Material	Die cast zinc	
Sale per indivisible quantity	1	
IP degree of protection	IP65 IEC 60529 IP657 IEC 60529	
Resistance to chemical agents	Special treatment can be obtained on request	

## Complementary

Number of vertical rows	1
Number of horizontal rows	1
Cut-out dimensions	Ø 22 mm
Cable entry	cable gland 1 x cable gland
Thread type	3/4 NPT
CAD overall width	3.1 in (80 mm)
CAD overall height	3.1 in (80 mm)
CAD overall depth	2.03 in (51.5 mm)
Product Weight	1.155 lb(US) (0.524 kg)
Compatibility code	XAPG

## **Environment**

Protective treatment	тн
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Electrical shock protection class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030
IK degree of protection	IK07 IEC 62262

# Ordering and shipping details

Category	US10CS222475	
Discount Schedule	0CS2	
GTIN	3389118381926	
Returnability	Yes	
Country of origin	MA	

# **Packing Units**

Unit Type of Package 1	PCE	
Nbr. of units in pkg.	1	
Package 1 Height	3.39 in (8.600 cm)	
Package 1 Width	3.54 in (9.000 cm)	
Package 1 Length	3.54 in (9.000 cm)	
Package weight(Lbs)	18.695 oz (530.000 g)	
Unit Type of Package 2	S02	
Number of Units in Package 2	12	
Package 2 Height	5.91 in (15.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	14.991 lb(US) (6.800 kg)	

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

<b>⊘</b> Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	4
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Offer Marketing Illustration

#### **Product benefits / Features**



### Offer Marketing Illustration

#### Product benefits / Features




Image of product / Alternate images

### **Alternative**











