



## Main

Range of Product	Harmony iPC
Product or Component Type	Serial line interface
Accessory / separate part category	Connection accessory

## Complementary

Accessory / separate part destination	Harmony iPC
Integrated connection type	Mini PCIe full-size 2 female SUB-D 9 RS422/RS485 50 bit/s...921.6 kbit/s 6.56 ft (2 m)
Input current	400 mA 3.3 V DC
Range Compatibility	Harmony iPC
Width	2.99 in (76 mm)
Height	3.19 in (81 mm)
Depth	1.50 in (38.2 mm)

## Environment

Ambient air temperature for operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Relative Humidity	5...95 % non-condensing

## Ordering and shipping details

Category	22574-MAGELIS BOX PC AND PANEL PC
Discount Schedule	MC2
GTIN	3606480795596
Returnability	No
Country of origin	TW

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.13 in (5.4 cm)
Package 1 Width	5.43 in (13.8 cm)
Package 1 Length	6.30 in (16.0 cm)
Package 1 Weight	1.41 oz (40.0 g)
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	17.35 oz (492.0 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.