

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product	Contacteur
Type	Type S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Contactor Type	Reversing
Number of Poles	2P
Phase	1 phase
Motor Wiring	3 wires
Line Rated Current	27 A
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
NEMA size	1
Height	5 in (127 mm)
Depth	5.31 in (135 mm)
Width	7.13 in (181 mm)

Environment

Enclosure Type	Not rated (open device)
Orientation	Horizontal
Product certifications	CSA UL listed

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901125457
Nbr. of units in pkg.	1
Package weight(Lbs)	7.140000000000006
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------