Product data sheet
Characteristics

AR3350X610
APC NetShelter SX, Server Rack Enclosure, 42U, without Doors, Black, 1991H x 750W x 1200D mm



Overview

Lead time	Usually in Stock

Main

Number of rack unit	42U
Provided equipment	Baying hardware Key(S) Leveling feet Mounting Hardware Pre-installed casters Side Panels

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	29.53 in (75 cm)
Depth	47.24 in (120 cm)
Net Weight	355.74 lb(US) (161.36 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	41.26 in (104.8 cm)
Minimum Mounting Depth	10.31 in (26.19 cm)
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge post 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E

Ordering and shipping details

GTIN	731304293811
Package weight(Lbs)	403.84 lb(US) (183.18 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Package 1 Height	83.39 in (211.8 cm)
Package 1 width	33.50 in (85.1 cm)
Package 1 Length	52.52 in (133.4 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace