



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Device short name	GVAS
Product or component type	Shunt trip
Device application	Control

Complementary

Product compatibility	GV2P GV3P GV3L GV2LE GV2ME GV2L
[Uc] control circuit voltage	500 V AC 50 Hz 600 V AC 60 Hz
Control circuit voltage limits	0.7...1.1 Un
[Ui] rated insulation voltage	600 V AC CSA C22.2 No 14 600 V AC UL 508 690 V AC IEC 60947-1
Threshold tripping voltage	0.75...0.2 Un
Inrush power in VA	14 VA AC
Inrush power in W	10.5 W DC
Hold-in power consumption in VA	5 VA AC
Hold-in power consumption in W	1.6 W DC
Operating time	10...15 ms IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 0.75...2.5 mm ² flexible without cable end Screw clamp terminals 2 0.75...2.5 mm ² flexible without cable end Screw clamp terminals 1 0.75...1.5 mm ² flexible with cable end Screw clamp terminals 2 0.75...1.5 mm ² flexible with cable end Screw clamp terminals 1 0...0 in ² (1...2.5 mm ²) solid
Tightening torque	< 1.4 N.m screw clamp terminals
Mechanical durability	10000 cycles with GV3P and GV3L 30000 cycles with GV2ME and GV2P
Quantity per set	Set of 10
Product weight	0.23 lb(US) (0.105 kg)

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901578369
Nbr. of units in pkg.	1
Package weight(Lbs)	0.25

Returnability	N
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

GVAS...

