

Product data sheet

Characteristics

ACAC10011

3ft (0.9144m) Stainless Flex Pipe Kit 1" MPT to 1" FPT Union



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Maximum Recommended Flow Rate	22 gal(US)/min (1.39 l/s)
Piping Material	Stainless steel
Pressure Rating	300 psi (2068.43 kPa)
Fluid connection type	NPT female NPT male
Minimum Fluid Temperature	42 °F (6 °C)
Maximum Fluid Temperature	55 °F (13 °C)
Pressure Drop per foot (0.305m)	0.92 ft of water/ft 19.97 gal(US)/min (1.26 l/s)

Physical

Length	3 ft (0.91 m)
Tube diameter	1 in (25.40 mm)
Product Weight	3.00 lb(US) (1.36 kg)

Ordering and shipping details

GTIN	00731304249221
Package weight(Lbs)	11.53 lb(US) (5.23 kg)

Packing Units

Package 1 Height	5.00 in (12.7 cm)
Package 1 width	29.02 in (73.7 cm)
Package 1 Length	29.02 in (73.7 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------