



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Main Output Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Input Connection Type	IEC 60320 C14
Number of rack unit	1U
Provided Equipment	Installation guide Safety guide

Physical

Color	Black
Height	9.45 in (24 cm)
Width	1.73 in (4.4 cm)
Depth	3.66 in (9.3 cm)
Net Weight	2.01 lb(US) (0.91 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Line Rated Current	12 A
Acceptable Input Voltage	100...240 V
Max line current	15 A
Input current limits	15 A
Load Capacity	2300 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

Conformance

Product Certifications	CUL Listed CE EAC IRAM UL Listed VDE
------------------------	---

Ordering and shipping details

GTIN	731304327790
Package weight(Lbs)	3.02 lb(US) (1.37 kg)

Packing Units

Package 1 Height	11.26 in (28.6 cm)
Package 1 width	8.27 in (21 cm)
Package 1 Length	5.12 in (13 cm)
SCC14	10731304327797
Number of Units in Package 3	192

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------