

Die cast empty control station, Harmony XAP, XB2 SL, zinc alloy, grey, 2 cut outs, 22mm, 80x130x77mm

XAPG29502

Product availability: Stock - Normally stocked in distribution facility

#### Main

Range of Product	Harmony XAP	
Product or Component Type	Die-cast empty control station	
Device short name	XAPG	
Product destination	For Ø 22 mm control and signalling units	
Product front plate size	80 x 130 mm	
Usable depth	2.9 in (74.5 mm)	
Number of cut-out	Undrilled	
Colour of base of enclosure	Grey RAL 7032)	
Colour of cover	Grey RAL 7032)	
Control station type	Metal	
Material	Die cast zinc	
Sale per indivisible quantity	1	
IP degree of protection	IP65 IEC 60529 IP657 IEC 60529	
Resistance to chemical agents	Special treatment can be obtained on request	

## Complementary

Number of vertical rows	1	
Number of horizontal rows	2	
Cut-out dimensions	Ø 22 mm	
Cable entry	cable gland 1 x cable gland	
Thread type	3/4 NPT	
CAD overall width	3.1 in (80 mm)	
CAD overall height	5.1 in (130 mm)	
CAD overall depth	3.03 in (77 mm)	
Product Weight	1.808 lb(US) (0.820 kg)	
Compatibility code	XAPG	

#### **Environment**

Protective treatment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient air temperature for operation	-13158 °F (-2570 °C)
Electrical shock protection class	Class I IEC 60536 Class I NF C 20-030
IK degree of protection	IK07 IEC 62262

# Ordering and shipping details

Category	US10CS222475	
Discount Schedule	0CS2	
GTIN	3389118381834	
Returnability	Yes	
Country of origin	MA	

# **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	3.74 in (9.500 cm)	
Package 1 Width	3.46 in (8.800 cm)	
Package 1 Length	6.10 in (15.500 cm)	
Package 1 Weight	2.235 lb(US) (1.014 kg)	
Unit Type of Package 2	S03	
Number of Units in Package 2	12	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	27.891 lb(US) (12.651 kg)	

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	7
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

### Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Offer Marketing Illustration

#### **Product benefits / Features**



### Offer Marketing Illustration

#### Product benefits / Features




Image of product / Alternate images

### **Alternative**





