

# ClimaSys forced vent. IP54, 38m3/h, 115V, with outlet grille and filter G2

NSYCVF38M115PF

Product availability: Stock - Normally stocked in distribution facility

### Main

Range	ClimaSys	
product name	ClimaSys CV	
Product or Component Type	Fan	
Type of filter	Standard	
Flow rate	Free flow rate with standard filter: 10038.7 Gal/hr(US) (38 m3/h) at 50 Hz Free flow rate with standard filter: 10302.9 Gal/hr(US) (39 m3/h) at 60 Hz	
[Us] rated supply voltage	75125 V	
Input voltage	115 V 50/60 Hz	

## Complementary

Absorbed power	3.3 W 50 Hz 3.5 W 60 Hz	
Line Rated Current	0.16 A 50 Hz 0.16 A 60 Hz	
Noise level < at	4041 dB	
Bearing type	Ball	
Height	External: 5.4 in (137 mm)	
Width	External: 4.6 in (117 mm)	
Depth	External : 1.9 in (49 mm)	
Cut-out dimensions	92 x 92 mm	
Net Weight	0.49 lb(US) (0.22 kg)	
Material	Outlet grille injected thermoplastic (ASA PC)	
color	Outlet grille Gray RAL 7035)	
Ambient Air Temperature for Operation	14158 °F (-1070 °C)	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Maximum pressure	29 Pa flow rate 0 m³/h	
Connections - Terminals	Cable	
IP degree of protection	IP54	
Device composition	axial motor     protective grille on the front and rear surfaces     filter front of axial motor	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

1 outlet grille front 1 cut-out template Condition of use

Outside temperature must be 5 °C lower than inside temperature

Flow rates depends on the work point, see ProClima software

Overfrequent filter replacement should be avoided Surrounding environment must be relatively clean Filter must be cleaned and replaced regularly

# Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606480151170
Returnability	Yes
Country of origin	FR

## **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	2.95 in (7.500 cm)	
Package 1 Width	4.92 in (12.500 cm)	
Package 1 Length	5.71 in (14.500 cm)	
Package 1 Weight	10.582 oz (300.000 g)	
Unit Type of Package 2	CAR	
Number of Units in Package 2	34	
Package 2 Height	23.62 in (60.000 cm)	
Package 2 Width	15.75 in (40.000 cm)	
Package 2 Length	10.83 in (27.500 cm)	
Package 2 Weight	23.501 lb(US) (10.660 kg)	
Unit Type of Package 3	PAM	
Number of Units in Package 3	340	
Package 3 Height	31.50 in (80.000 cm)	
Package 3 Width	39.37 in (100.000 cm)	
Package 3 Length	47.24 in (120.000 cm)	
Package 3 Weight	282.192 lb(US) (128.000 kg)	

## **Contractual warranty**

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

### Environmental footprint

Environmental Disclosure

Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	61d9d3f3-5a49-48f8-8056-1a5ad0ad4c76
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No