

Product data sheet

Characteristics

8910DPA32V14

Contactor, Definite Purpose, 30A, 2 pole, 5 HP at 230VAC, 1 phase, 24VAC coil at 50/60Hz, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	24 V AC 50/60 Hz
Phase	1 phase
Electrical Connection	Binder head Quick connect terminals

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details





Category	21343-8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	785901749820
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.20 in (8.128 cm)
Package 1 Width	4.10 in (10.414 cm)
Package 1 Length	2.60 in (6.604 cm)
Package 1 Weight	16.32 oz (462.664 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	6.90 in (17.526 cm)
Package 2 Width	5.60 in (14.224 cm)

Package 2 Length	8.60 in (21.844 cm)
Package 2 Weight	8.44 lb(US) (3.828 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------