SQUARE D



# 30mm Push Button, Types K, SK or KX, light module, yellow LED lamp, 24/28 VAC/VDC

9001KM35LY

Product availability: Stock - Normally stocked in distribution facility

## Main

| Range of Product          | Harmony 9001K<br>Harmony 9001SK        |  |
|---------------------------|--|--|
| Product or Component Type | Light module<br>Light block            |  |
| Device short name         | 9001K                                  |  |
| Bulb base                 | BA 9s                                  |  |
| Light block supply        | Direct via integral resistance 0.28 VA |  |

## **Complementary**

| Light source              | LED (bulb included) |  |
|---------------------------|---------------------|--|
| Light block colour        | Yellow              |  |
| [Us] rated supply voltage | 2428 V AC 5060 Hz   |  |

## **Environment**

| Protective treatment                  | TC   |  |
|---------------------------------------|--|--|
| Ambient Air Temperature for Storage   | -40158 °F (-4070 °C)<br>-4070 °C (-40158 °F)   |  |
| Ambient Air Temperature for Operation | -13158 °F (-2570 °C)<br>-2570 °C (-13158 °F)   |  |
| IP degree of protection               | IP20 IEC 60529   |  |
| Standards                             | UL 508 CSA C22.2 No 14 EN/IEC 60947-5-4 EN/IEC 60947-5-1 EN/IEC 60947-1 JIS C 4520 JIS C 852 |  |
| Product Certifications                | UL Listed<br>CSA<br>NEMA   |  |
| Electrical shock protection class     | Class II conforming to IEC 61140   |  |
| Vibration resistance                  | 7 gn (f= 2500 Hz) conforming to IEC 60068-2-6  |  |
| Shock resistance                      | 50 gn IEC 60068-2-27   |  |

## Ordering and shipping details

| Category          | US10CS121435 |
|-------------------|--------------|
| Discount Schedule | 0CS1         |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| GTIN              | 785901029007 |
|-------------------|--------------|
| Returnability     | Yes          |
| Country of origin | MX           |

# **Packing Units**

| Unit Type of Package 1       | PCE              |
|------------------------------|------------------|
| Number of Units in Package 1 | 1                |
| Package 1 Height             | 2.01 in (5.1 cm) |
| Package 1 Width              | 2.28 in (5.8 cm) |
| Package 1 Length             | 3.70 in (9.4 cm) |
| Package 1 Weight             | 2.6 oz (72.6 g)  |

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

### **Use Better**

| Packaging made with recycled cardboard | Yes   |
|--|---|
| Packaging without single use plastic   | Yes   |
| EU RoHS Directive                      | Pro-active compliance (Product out of EU RoHS legal scope)  |
| SCIP Number                            | Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d  |
| REACh Regulation                       | REACh Declaration   |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

### **Use Again**

| ○ Repack and remanufacture |  |
|----------------------------|--|
| Take-back                  | No   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |