

PDPM144F

APC Modular Remote Power Panel, 144kVA,
400A, 208V, 72 Pole, 300mm



Overview

Presentation	A fully scalable power distribution system that cost-effectively provides high levels of availability and enables the quick addition of circuits and cord-sets.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	3 phase
Main Output Voltage	208 V 3 phase
Provided Equipment	Installation guide

Physical

Height	78.82 in (200.2 cm)
Width	11.81 in (30 cm)
Depth	42.40 in (107.7 cm)
Net Weight	352.74 lb(US) (160 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz
Acceptable Input Voltage	200...240 V
Max line current	400 A

Output

Maximum Total Current Draw per Phase	400 A
--------------------------------------	-------

Conformance

Product Certifications	UL Listed
Standards	OSHPD


Ordering and shipping details

GTIN	731304271611
Package weight(Lbs)	401.84 lb(US) (182.27 kg)

Packing Units

Package 1 Height	88.50 in (224.8 cm)
Package 1 width	33.50 in (85.1 cm)
Package 1 Length	47.48 in (120.6 cm)

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------