

Multisound siren, Harmony XVS, prewired, white colour, 0...105dB, 43tones, 12...24V DC

XVS14BMW

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XVS
Product or Component Type	Multisound siren
Device short name	XVS

Complementary

Color	White	
Material	ASA (Acrylonitrile Styrene Acrylate): front ASA (Acrylonitrile Styrene Acrylate): back PC (polycarbonate): back cover	
Net Weight	2.2 lb(US) (1 kg)	
Marking	CE	
Mounting Support	Bracket	
Fixing Mode	3 holes Ø 9 mm	
[Uimp] rated impulse withstand voltage	0.8 kV	
Current consumption	350 mA 24 V 250 mA 12 V	
Electrical connection	Cable 0.30.3 in (6.58.5 mm), 0.0005 in² (0.33 mm²) / AWG 22 signalling circuit) Cable 0.30.3 in (6.58.5 mm), 0.0008 in² (0.52 mm²) / AWG 20 power circuit)	
Width	5.5 in (140 mm)	
Height	4.5 in (114 mm)	
Depth	8.8 in (223 mm)	

Environment

Signalling type	43 tones siren	
Standards	IEC 61000-6-2	
	EN 55014-2	
	EN 55022	
	IEC 61000-6-3	
Product Certifications	UL	
Protective treatment	TC	
Ambient Air Temperature for Storage	-31158 °F (-3570 °C)	
Ambient Air Temperature for Operation	14122 °F (-1050 °C)	
Overvoltage category	Class II conforming to IEC 61140	
IP degree of protection	IP53 conforming to IEC 60529	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Noise level	0 105 dB continuous or intermittent tone)1 m
	24 V DC
[Us] rated supply voltage	12 V DC

Ordering and shipping details

Category	US100XV22617	
Discount Schedule	00XV	
GTIN	3606480032943	
Returnability	Yes	
Country of origin	ID	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	10.83 in (27.500 cm)	
Package 1 Width	6.30 in (16.000 cm)	
Package 1 Length	6.30 in (16.000 cm)	
Package 1 Weight	2.954 lb(US) (1.340 kg)	
Unit Type of Package 2	S04	
Number of Units in Package 2	6	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	15.75 in (40.000 cm)	
Package 2 Length	23.62 in (60.000 cm)	
Package 2 Weight	20.507 lb(US) (9.302 kg)	

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	13
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Fe0ee3ab-dd49-4abe-bd8e-c49754e2c442
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again


○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No


Dimensions Drawings

Siren

Dimensions







Technical Illustration

Dimensions




Image of product / Alternate images

Alternative









