

ClimaSys forced vent. IP54, 300m3/h, 115V, with outlet grille and filter G2

NSYCVF300M115PF

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually Ships within 4 Weeks

Main

Range	ClimaSys	
Product name	ClimaSys CV	
Product or Component Type	Fan	
Type of filter	Standard	
Flow rate	Free flow rate with standard filter: 79253.03 Gal/hr(US) (300 m3/h) at 50 Hz Free flow rate with standard filter: 92461.9 Gal/hr(US) (350 m3/h) at 60 Hz	
[Us] rated supply voltage	75126 V	
Input voltage	115 V 50/60 Hz	
Certification	CSA	

Complementary

Absorbed power	36 W 50 Hz	
	36 W 60 Hz	
Line Rated Current	0.35 A 50 Hz	
	0.32 A 60 Hz	
Noise level < at	6068 dB	
Bearing type	Ball	
Height	External: 10.6 in (268 mm)	
Width	External: 9.8 in (248 mm)	
Depth	External : 4.6 in (116 mm)	
Cut-out dimensions	223 x 223 mm	
Net Weight	2.9 lb(US) (1.3 kg)	
Material	Outlet grille injected thermoplastic (ASA PC)	
color	Outlet grille Gray RAL 7035)	
Ambient Air Temperature for Operation	14158 °F (-1070 °C)	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Maximum pressure	158 Pa flow rate 0 m³/h	
Connections - Terminals	Faston connector	
IP degree of protection	IP54	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Device composition	axial motor protective grille on the front and rear surfaces filter front of axial motor outlet grille front cut-out template power cord
Condition of use	Flow rates depends on the work point, see ProClima software Surrounding environment must be relatively clean Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Overfrequent filter replacement should be avoided

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606480151293
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.28 in (18.500 cm)
Package 1 Width	9.84 in (25.000 cm)
Package 1 Length	10.83 in (27.500 cm)
Package 1 Weight	3.792 lb(US) (1.720 kg)
Unit Type of Package 2	P12
Number of Units in Package 2	64
Package 2 Height	47.24 in (120.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	277.783 lb(US) (126.000 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	61d9d3f3-5a49-48f8-8056-1a5ad0ad4c76
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No