

Product data sheet

Characteristics

8910DPA32V02

Contactor, Definite Purpose, 30A, 2 pole, 5 HP at 230VAC, 1 phase, 110/120VAC coil at 50/60Hz, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	1 phase
Electrical Connection	Binder head Quick connect terminals
Height	2.31 in (58.67 mm) 2.31 in (58.70 mm)
Width	2.37 in (60.20 mm) 2.37 in (60.2 mm)
Depth	2.90 in (73.66 mm) 2.99 in (76 mm)
Net Weight	0.97 Lb(US) (0.44 kg) 0.98 lb(US) (0.44 kg)

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------





Ordering and shipping details

Category	21343-8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	785901116967
Nbr. of units in pkg.	1
Package weight(Lbs)	15.68 oz (444.521 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.50 in (6.35 cm)
Package 1 width	3.10 in (7.874 cm)
Package 1 Length	4.00 in (10.16 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Weight	8.13 lb(US) (3.688 kg)
Package 2 Height	6.80 in (17.272 cm)
Package 2 width	5.40 in (13.716 cm)
Package 2 Length	8.10 in (20.574 cm)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

