

Light block, Harmony 9001K, Harmony 9001SK, 30mm, incandescent bulb, 24...28V

9001KM35

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony 9001K Harmony 9001SK
Product or Component Type	Light block
Device short name	9001K
Bulb base	BA 9s
Light block supply	Direct via integral resistance

Complementary

Net Weight	0.11 lb(US) (0.05 kg)	
Light source	Incandescent bulb	
[Us] rated supply voltage	24 V AC/DC	
[Us] rated supply voltage	2428 V	
Light block supply	Full voltage	
Size	30 mm	

Environment

Protective treatment	TC	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)	
IP degree of protection	IP20 IEC 60529	
Standards	IEC 60947-5-4 JIS C 852 UL 508 IEC 60947-1 CSA C22.2 No 14 JIS C 4520 IEC 60947-5-1	
Product Certifications	NEMA UL 508	
Electrical shock protection class	Class II conforming to IEC 61140	
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn IEC 60068-2-27	

Ordering and shipping details

Category US10CS121435

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CS1
GTIN	785901726524
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.20 in (5.588 cm)
Package 1 Width	3.60 in (9.144 cm)
Package 1 Length	1.90 in (4.826 cm)
Package 1 Weight	2.240 oz (63.503 g)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture		
Take-back	No	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	

Dimensions Drawings

Dimensions



 \boldsymbol{e} panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001K



Jul 4, 2025