

30mm Push Button, Type SK, push pull operator, red mushroom cap

9001SKR9R

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony 9001SK	
Product or Component Type	Head for push-button	
Device short name	9001SK	

Complementary

Bezel material	Plastic
Mounting diameter	1.2 in (30 mm)
CAD overall width	1.8 in (46 mm)
CAD overall height	1.8 in (45 mm)
CAD overall depth	2.7 in (69 mm)
Net Weight	0.209 lb(US) (0.095 kg)
Operating position	Any position
Shape of signaling unit head	Round
Type of operator	maintained
Operator profile	mushroom Ø 41 mm, unmarked
Mechanical durability	5000000 cycles
Operator additional information	Screw-on plastic
Cap/operator or lens colour	Red
Operator profile	Mushroom Ø 41 mm
Type of operator	Push-pull
Operator position information	2 positions
Contacts type and composition	Without contact block
Size	30 mm

Environment

Protective treatment	TC
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Enclosure Type	NEMA 1 NEMA 12 NEMA 13	
	NEMA 2	
	NEMA 3	
	NEMA 3R	
	NEMA 4	
	NEMA 4X	
Standards	CSA C22.2 No 14	
	EN/IEC 60947-5-1	
	EN/IEC 60947-1	
	EN/IEC 60947-5-4	
	JIS C 4520	
	JIS C 852	
	UL 508	
Product Certifications	UL 508	
	NEMA	
	CSA LR25490 class 3211 03	
	UL listed file E78403 CCN NKCR	
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn IEC 60068-2-27	

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
GTIN	3389118036406
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	2.081 oz (59.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	6.881 lb(US) (3.121 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	800
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	130.869 lb(US) (59.361 kg)

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	1	

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001SK



Offer Marketing Illustration

Product benefits / Features



Image of product / Alternate images

Alternative







