



Main

Range	9002AW
Product	Foot switch
Contact Operation	4 steps
Certifications	CSA UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT per step
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Side shield Oversized pedal shield Safety door
Operator Action	Spring return
Rated Breaking Capacity	1.5 A 120 V AC inductive control circuit UL 508 0.75 A 240 V AC inductive control circuit UL 508 0.375 A 480 V AC inductive control circuit UL 508 0.3 A 600 V AC inductive control circuit UL 508
Height	6.26 in (159 mm)
Width	6.42 in (163 mm)
Depth	11.14 in (283 mm)

Ordering and shipping details

Category	21441-9002 AW FOOT SWITCHES
Discount Schedule	CS1
GTIN	785901846314
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.24 in (38.71 cm)
Package 1 Width	6.00 in (15.24 cm)
Package 1 Length	38.71 in (98.322 cm)
Package 1 Weight	12.00 lb(US) (5.443 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------