SQUARE D



Contactor, Definite Purpose, 60A, 3 pole, 30HP at 575VAC, 3 phase, 110/120VAC 50/60Hz coil, open, hex head screw

8910DPA63V02Y125

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	60 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA
Enclosure Type	No enclosure

Complementary

Maximum Horse Power Rating	5 hp 115 V AC, 1 phase		
	10 hp 230 V AC, 1 phase 30 hp 460 V AC, 3 phase		
	30 hp 575 V AC, 3 phase		
	25 hp 230 V AC, 3 phase		
Locked rotor rated current	360 A 230 V AC		
	300 A 460 V AC		
	240 A 575 V AC		
[Ue] rated operational voltage	600 V AC		
[Uc] control circuit voltage	120 V AC 60 Hz		
	110 V AC 50 Hz		
Phase	3 phase		
Electrical Connection	Box lugs		
Mounting Support	Surface mount		

Environment

Product Certifications	UL Recognized	
	CSA	

Ordering and shipping details

Category	US1CP1B21346
Discount Schedule	CP1B
GTIN	785901965411
Returnability	No
Country of origin	CN

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.610 lb(US) (1.184 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions

Use Again

○ Repack and remanufacture		
Take-back	No	

Technical Illustration

Wiring diagram

