

# 8910DPA32V06

## CONTACTOR 600VAC 30AMP DPA +OPTIONS

Product availability: Stock - Normally stocked in distribution facility



### Main

Product or component type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	2P
Pole contact composition	2 NO
Range of product	DPA

### Complementary

Motor power hp	2 hp 115 V AC 1 phase 5 hp 230 V AC 1 phase
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
System Voltage	600 V AC
[Uc] control circuit voltage	440 V AC 50 Hz 480 V AC 60 Hz
Phase	1 phase
Electrical connection	Quick connect terminals Binder head

### Environment

Product certifications	CE CSA UL listed
------------------------	------------------------

### Ordering and shipping details

Category	21343 - 8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	00785901024415
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	Y
Country of origin	CN

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1140 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------