



Overview

Presentation	Wide modular battery cabinet with up to a 12 string modular battery capacity. To be used with GVMMBTU battery string. Batteries are not included in the SKU and must be purchased separately.
Lead time	Usually Ships within 2 Weeks

Main

Main Input Voltage	3 phase
Battery Type	VRLA
Provided Equipment	Installation guide

Physical

Color	White
Height	77.56 in (197 cm)
Width	27.56 in (70 cm)
Depth	33.62 in (85.4 cm)
Net Weight	462.97 lb(US) (210 kg)

Input

Input Frequency	40 - 70 Hz
-----------------	------------

Conformance

Standards	EN/IEC 62040-3 FCC Part 15 class A OSHPD UL 1778
-----------	---

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...49212 ft (0.00...14999.82 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Battery Cabinet
Battery Slots Empty	12
Included Battery Modules	0
Device mounting	Enclosed battery cabinet
Battery Voltage	480V

Ordering and shipping details

GTIN	731304311263
Package weight(Lbs)	555.57 lb(US) (252 kg)

Packing Units

Package 1 Height	84.65 in (215 cm)
Package 1 width	38.98 in (99 cm)
Package 1 Length	41.73 in (106 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---