

ClimaSys forced vent. IP54, 85m3/h, 115V, with outlet grille and filter G2

NSYCVF85M115PF

Product availability: Stock - Normally stocked in distribution

Main

Range	ClimaSys	
Product name	ClimaSys CV	
Product or Component Type	Fan	
Type of filter	Standard	
Flow rate	Free flow rate with standard filter: 20870.0 Gal/hr(US) (79 m3/h) at 50 Hz Free flow rate with standard filter: 24304.3 Gal/hr(US) (92 m3/h) at 60 Hz	
[Us] rated supply voltage	75126 V	
Input voltage	115 V 50/60 Hz	
Certification	CSA	

Complementary

Absorbed power	15 W 60 Hz 16 W 50 Hz	
Line Rated Current	0.207 A 50 Hz 0.179 A 60 Hz	
Noise level < at	4649 dB	
Bearing type	Ball	
Height	External: 6.7 in (170 mm)	
Width	External: 5.9 in (150 mm)	
Depth	External : 2.4 in (62 mm)	
Cut-out dimensions	125 x 125 mm	
Net Weight	1.72 lb(US) (0.78 kg)	
Material	Outlet grille injected thermoplastic (ASA PC)	
color	Outlet grille Gray RAL 7035)	
Ambient Air Temperature for Operation	-4140 °F (-2060 °C)	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Maximum pressure	50 Pa flow rate 0 m³/h	
Connections - Terminals	Faston connector	
IP degree of protection	IP54	
Device composition	axial motor protective grille on the front and rear surfaces filter front of axial motor outlet grille front	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

1 cut-out template 1 power cord

Life Is On Schneider Jul 12, 2025



Condition of use Overfrequent filter replacement should be avoided

Surrounding environment must be relatively clean

Outside temperature must be 5 $^{\circ}$ C lower than inside temperature Flow rates depends on the work point, see ProClima software

Filter must be cleaned and replaced regularly

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606480151217
Returnability	Yes
Country of origin	FR

Packing Units

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.35 in (8.500 cm)
Package 1 Width	6.10 in (15.500 cm)
Package 1 Length	7.28 in (18.500 cm)
Package 1 Weight	32.275 oz (915.000 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	8.27 in (21.000 cm)
Package 2 Width	12.99 in (33.000 cm)
Package 2 Length	16.93 in (43.000 cm)
Package 2 Weight	21.001 lb(US) (9.526 kg)
Unit Type of Package 3	PAM
Number of Units in Package 3	240
Package 3 Height	41.34 in (105.000 cm)
Package 3 Width	39.37 in (100.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	533.519 lb(US) (242.000 kg)

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	61d9d3f3-5a49-48f8-8056-1a5ad0ad4c76
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No