

Monolithic pre wired tower light, Harmony XVC, plastic, red orange green, 60mm, base mounting, steady or flashing, buzzer, IP54, 24V AC DC

XVC6B35SK

Product availability: Stock - Normally stocked in distribution facility

Main

| Range of Product | Harmony XVC6 |
|------------------------------------|---|
| Product or Component Type | Complete pre-wired monolithic tower light |
| Beacon or indicator bank unit type | 3 illuminated units |
| Sound signalling | Buzzer |
| Mounting diameter | 2.4 in (60 mm) |
| Component name | XVC |
| Light source | LED steady or flashing red LED steady or flashing orange LED steady or flashing green |
| [Us] rated supply voltage | 24 V |
| Supply circuit type | AC/DC |
| Noise level | 7085 dB continuous or intermittent tone)1 m |

Complementary

| Material | Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover |
|--|--|
| Product mounting | On base |
| Cable cross section | 0.0005 in² (0.33 mm²) |
| AWG Gauge | AWG 22 |
| Cable length | 33.5 in (850 mm) |
| Marking | CE |
| [Uimp] rated impulse withstand voltage | 0.8 kV |
| Current Consumption | 115 mA |
| Fundamental frequency | 2.23 kHz |
| Flashing frequency | 1 Hz |
| Net Weight | 0.7 lb(US) (0.3 kg) |
| Height | 7.9 in (200.8 mm) |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Standards | IEC 61000-6-4 IEC 61000-6-3 IEC 61000-6-2 |
|---------------------------------------|---|
| Product Certifications | UL |
| Protective treatment | тс |
| Ambient Air Temperature for Storage | -31158 °F (-3570 °C) |
| Ambient Air Temperature for Operation | 14122 °F (-1050 °C) |
| Electrical shock protection class | Class II conforming to IEC 61140 |
| IP degree of protection | IP54 flat surface installation IEC 60529 |

Ordering and shipping details

| Category | US100XV22617 |
|-------------------|---------------|
| Discount Schedule | 00XV |
| GTIN | 3606480032714 |
| Returnability | Yes |
| Country of origin | ID |

Packing Units

| Unit Type of Package 1 | PCE |
|------------------------------|--------------------------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.46 in (8.800 cm) |
| Package 1 Width | 3.35 in (8.500 cm) |
| Package 1 Length | 19.88 in (50.500 cm) |
| Package 1 Weight | 18.624 oz (528.000 g) |
| Unit Type of Package 2 | S04 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 11.81 in (30.000 cm) |
| Package 2 Width | 15.75 in (40.000 cm) |
| Package 2 Length | 23.62 in (60.000 cm) |
| Package 2 Weight | 14.489 lb(US) (6.572 kg) |

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ☑ Environmental footprint | | |
|--|----|--|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 25 | |

Use Better

| Materials and Substances | |
|--|---|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Again

| ○ Repack and remanufacture | | |
|----------------------------|----|--|
| Take-back | No | |


XVC6B35SK


Dimensions Drawings

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.





| No. of illuminated units | b (mm) | b (in.) |
|--------------------------|--------|---------|
| 1 stage | 120.8 | 4.76 |
| 2 stages | 160.8 | 6.33 |
| 3 stages | 200.8 | 7.90 |
| 4 stages | 240.8 | 9.48 |
| 5 stages | 280.8 | 11.06 |

Product data sheet


XVC6B35SK

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out



Technical Illustration

Dimensions




Image of product / Alternate images

Alternative











