

Emergency stop head, Harmony 9001SK, switching off, plastic, red mushroom 40mm, 30 mm, trigger and latching turn to release

9001SKR16

Product availability: Stock - Normally stocked in distribution facility

#### Main

Range of Product	Harmony 9001SK	
Product or Component Type	Head for emergency switching off push-button	
Device short name	9001SK	

#### Complementary

Bezel material	Plastic	
Mounting diameter	1.2 in (30 mm)	
CAD overall width	1.6 in (40 mm)	
CAD overall height	1.6 in (40 mm)	
CAD overall depth	3.5 in (90 mm)	
Net Weight	0.311 lb(US) (0.141 kg)	
Operating position	Any position	
Shape of signaling unit head	Round	
Type of operator	turn to release trigger action maintained	
Operator profile	Red mushroom Ø 40 mm, CE	
Mechanical durability	5000000 cycles	
Cap/operator or lens colour	Red	
Operator profile	Mushroom Ø 40 mm	
Type of operator	Turn to release	
Operator position information	2 positions	
Contacts type and composition	Without contact block	
Size	30 mm	

#### **Environment**

Protective treatment	TC
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient air temperature for operation	-13158 °F (-2570 °C)
Electrical shock protection class	Class II IEC 61140
IP degree of protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3 NEMA 4 NEMA 4	
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 JIS C 4520 JIS C 852 UL 60947-5-5	
Product Certifications	NEMA UL listed file E78403 CCN NKCR CSA LR25490 class 3211 03 UL 508	
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn IEC 60068-2-27	

# Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
GTIN	3389118372559	
Returnability	Yes	
Country of origin	MX	

## **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	2.40 in (6.096 cm)	
Package 1 Width	2.10 in (5.334 cm)	
Package 1 Length	4.60 in (11.684 cm)	
Package 1 Weight	3.040 oz (86.182 g)	

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Materials and Substances	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
China RoHS Regulation	China RoHS declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


#### Use Again

○ Repack and remanufacture		
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Take-back	No	

### 9001SKR16

#### **Dimensions Drawings**

#### **Dimensions**




e: panel thickness 1 to 6 mm / 0.04 to 0.24 in.

#### Mounting and Clearance

#### **Contact Block Mounting Position**

Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2