

# Selector switch head, Harmony 9001K, metal, long handle, black, 30mm, 4 positions, stay put

9001KS88FB

Product availability: Stock - Normally stocked in distribution facility

#### Main

Range of Product	Harmony 9001K
Product or Component Type	Head for selector switch
Device short name	9001K
Type of operator	stay put
Operator profile	Black long handle

#### Complementary

Bezel material	Metal
Mounting diameter	1.2 in (30 mm)
Net Weight	0.379 lb(US) (0.172 kg)
Shape of signaling unit head	Octagonal
Operator position information	4 positions
Contacts type and composition	Without contact block
Mechanical durability	500000 cycles
Product compatibility	9001KA1 side 1 and 2
Device presentation	Basic element
Cap/operator or lens colour	Black
Operator profile	Long handle
Type of operator	Stay put
Size	30 mm
Cam profile	8

#### **Environment**

Protective treatment	TC
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

NEMA degree of protection	NEMA 1	
	NEMA 12	
	NEMA 13	
	NEMA 2	
	NEMA 3	
	NEMA 3R	
	NEMA 4	
Standards	UL 508	
	IEC 60947-5-4	
	JIS C 852	
	CSA C22.2 No 14	
	JIS C 4520	
	IEC 60947-5-1	
	IEC 60947-1	
Product Certifications	UL 508	
	NEMA	
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn IEC 60068-2-27	

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
GTIN	785901959250
Returnability	Yes
Country of origin	US

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.13 in (5.400 cm)
Package 1 Width	1.81 in (4.600 cm)
Package 1 Length	3.90 in (9.900 cm)
Package 1 Weight	4.409 oz (125.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	10.505 lb(US) (4.765 kg)

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


#### **Use Again**

○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

#### **Dimensions Drawings**

#### **Dimensions**






 $\boldsymbol{e}$  panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

## 9001KS88FB

#### Mounting and Clearance

#### **Contact Block Mounting Position**


#### Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

#### Panel Cut-Out

#### Clearance



Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

#### **Individual Cut-outs Details**

#### 2 alternatives

