



Foot Switch, Harmony, industrial, unshielded, maintained contact, 3A at 230 VAC, SPST contact, NEMA 2, 4, 13 enclosure

9002AW11

Product availability: Stock - Normally stocked in distribution facility

Main

| Range | 9002AW | |
|-------------------------|---|--|
| Product | Foot switch | |
| Contact Operation | 1 step | |
| Certifications | CSA UL Listed | |
| Cable Entry | 0.75 inch NPT conduit entrance | |
| Contact Arrangement | SPST | |
| Enclosure Rating | NEMA 2/4/13 | |
| Voltage Rating | 600 V AC/DC | |
| Protection | Unshielded | |
| Operator Action | Maintained | |
| Rated Breaking Capacity | 6 A 115 V AC inductive control circuit UL 508 3 A 230 V AC inductive control circuit UL 508 2.2 A 125 V DC inductive control circuit UL 508 2.2 A 125 V DC resistive control circuit UL 508 1.1 A 250 V DC inductive control circuit UL 508 1.1 A 250 V DC resistive control circuit UL 508 | |
| Height | 3.9 in (99 mm) | |
| Width | 4.5 in (114 mm) | |
| Depth | 8.5 in (216 mm) | |

Ordering and shipping details

| e i i e | | |
|-------------------|--------------|--|
| Category | US10CS121441 | |
| Discount Schedule | 0CS1 | |
| GTIN | 785901816737 | |
| Returnability | Yes | |
| Country of origin | MX | |

Packing Units

| Unit Type of Package 1 | PCE | |
|------------------------------|---------------------|--|
| Number of Units in Package 1 | 1 | |
| Package 1 Height | 3.30 in (8.382 cm) | |
| Package 1 Width | 4.90 in (12.446 cm) | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Length | 9.10 in (23.114 cm) |
|------------------|-------------------------|
| Package 1 Weight | 3.100 lb(US) (1.406 kg) |

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ∇ Environmental footprint | |
|--|-------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 10 |
| Environmental Disclosure | Product Environmental Profile |

Use Better

| Materials and Substances | |
|--|--|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | Yes |
| China RoHS Regulation | China RoHS declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Again

| ○ Repack and remanufacture | |
|----------------------------|--|
| Circularity Profile | No need of specific recycling operations |
| Take-back | No |