

# 30mm Push Button, Type K, joystick controller, 5 positions, spring return, without contacts

9001K35

Product availability: Stock - Normally stocked in distribution facility

#### Main

Range of Product	Harmony 9001K
Product or Component Type	Head for joystick controller
Device short name	9001K
Sale per indivisible quantity	1
Type of operator	spring return
Operator profile	80 mm long operating shaft

#### Complementary

•	
Bezel material	Metal
Mounting diameter	1.2 in (30 mm)
Net Weight	0.820 lb(US) (0.372 kg)
Operating position	Any position
Shape of signaling unit head	Octagonal
Contacts type and composition	Without contact block
Device presentation	Basic element
Operator direction information	4 directions
Type of operator	Spring return
Size	30 mm
Return	To centre

#### **Environment**

Protective treatment	TC
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)
Overvoltage category	II conforming to IEC 61140
IP degree of protection	IP66 IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3R NEMA 4

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	JIS C8201-5-1 JIS C 852 CSA C22.2 No 14 IEC 60947-5-1 UL 508 IEC 60947-1	
	IEC 60947-5-4	
	JIS C8201-1	
Product Certifications	UL 508 NEMA	
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn IEC 60068-2-27	

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
GTIN	785901077145
Returnability	Yes
Country of origin	MX

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	1.65 in (4.200 cm)
Package 1 Length	5.28 in (13.400 cm)
Package 1 Weight	8.501 oz (241.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	18
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	10.214 lb(US) (4.633 kg)

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


#### **Use Again**

○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

#### Mounting and Clearance

#### **Contact Block Mounting Position**


#### Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

#### Panel Cut-Out


#### Clearance




Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

#### **Individual Cut-outs Details**


#### 2 alternatives





**Technical Description** 

#### **Joystick Positions**



#### 9001K35

Offer Marketing Illustration

#### **Product benefits / Features**



#### Offer Marketing Illustration

#### **Product benefits / Features**

#### **Technical Benefits**

#### Harmony 9001K



## Product data sheet

### 9001K35

Image of product / Alternate images

**Alternative** 







