



Overview

Presentation	An industry-standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office branch office spaces for a secure and discrete solution for IT devices.
Lead time	Usually in Stock

Main

Number of rack unit	18U
Provided equipment	Casters Doors Key(S) Leveling feet Roof Side Panels

Physical

Color	Black
Height	36.42 in (92.5 cm)
Width	23.62 in (60 cm)
Depth	35.43 in (90 cm)
Net Weight	148.00 lb(US) (67.13 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	29.75 in (75.57 cm)
Minimum Mounting Depth	7.52 in (19.1 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	900 Lb(US) (408.23 kg) dynamic 900 lb(US) (408.23 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304347651
Package weight(Lbs)	189.60 lb(US) (86 kg)

Packing Units

Package 1 Height	41.73 in (106 cm)
Package 1 width	29.53 in (75 cm)
Package 1 Length	39.17 in (99.5 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------